

NWD602

ELECTRIC BED



NWD602

FEATURES AND HIGHLIGHTS




Technical parameters

▪ External size (LxW)	2150x980(±10mm)
▪ Height adjustment	440-640mm(±10mm)
▪ Mattress platform	1950x900mm
▪ Back-rest adjustment	0-75° (±10°)
▪ Knee-rest adjustment	0-35° (±10°)
▪ Safe working load	200 kg
▪ Voltage 100-230 V	
▪ Frequency 50/60 Hz	

Technical configuration

☑ Linear motor	3pcs
☑ 5" covered castors	4pcs
☑ ABS side rail extra height	1set
☑ ABS bed ends with safe lock	1set
☑ Hand controller	1pc
☑ IV pole prevision	4pcs
☑ Drainage hook	2pcs



Design

The simple and elegant head and foot board design of the bed meets the hospital's infection control requirements and supports daily disinfection operations.



Plastic

Environmentally friendly plastic, non-toxic and odorless



Painting

The overall bed body adopts a series of processes of pickling, phosphating, water washing and oxidation, and a fully automatic water spraying line uses powder electrostatic spraying process to achieve bright color and firm adhesion.



Welding

Aluminum alloy side rail, 6-staff, collapsed type with safe lock.



Electric Control System

Famous brand motor has passed UL medical certification, stable performance, and motor noise of 50dB.



Hand Controller

The hand controller has a flexible spring wire, which makes it convenient and flexible to operate the hospital bed in the best position. Nurses can easily control all standard functions, including one-button CPR and background light function.



Platform

The bed width is 900mm, using a four-piece bed board, made of high-quality cold-rolled steel plate stamped at one time, with a thickness of 1.0mm, and a multi-hole design for easy ventilation and anti-slip function. There are no solder joints on the surface, and there are steel pipe reinforcements on the back. It adopts a double-support unloading structure to extend the life of the hospital bed and has a load-bearing capacity of 200KG.



Siderail

C-type guardrail, with angle display function, made of PP engineering plastic, beautiful appearance, easy to operate, sturdy and durable, easy to clean, anti-pinch design, the guardrail lift uses a damper device to control speed and noise, and can be hidden under the bed panel when lowered flush with bed frame



Head & Foot Board

Simple and elegant bed head and foot shape, easy to disassemble and install, with medical record card at the foot of the bed




Castor

Use medical silent wheels with a diameter of 125mm, and each caster has a brake



Drainage Hook

There are drainage hooks on both sides of the bed.





NUMBER WIN

MEDICAL TECHNOLOGY



7×24

Online 24 Hours for Sales Service
Timely Response for Clients' Problems

+86 18021239272

Suzhou Number Win Medical Technology Co.,Ltd.

No. 35, Lehong Road · Zhangjiagang (Jiangsu) · China

export@number-win.com

www.number-win.com

As the circumstance of printing, the photos might have minor difference on color, tactile from real products.
As the update of design and improvement, parameters and outlook of products might change, thanks for understanding.



Company video



General catalogue